



**Catalog No. TGN3321**

**Description: 30A 3P GD N1 240V NONFUSE SWITCH**

**UPC No 783164008784**

**Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > General Duty**

- Designed for residential and light commercial applications where duty is not severe.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Certified to CSA standard 22.2 no. 4-04 enclosed and dead front switches.
- Meets or exceeds NEMA KS1 standard for enclosed switches - type GD.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism (30-200 amp).
- 60/75°C conductor rating.

**Descriptors**

Category	General Duty
----------	--------------

**Specifications**

Amperage	30 A
Poles	3
Wires	3
Fusing	No Fuse
Enclosure	NEMA 1 (Indoor)
Wire Range (Cu/Al)	12-8 AL, 14-8 CU
240 Vac, NEC Std, 1-ph	3
240 Vac, NEC Std, 3-ph	7.5
250 Vdc	5
GSA Compliance	Yes

**Classifications**

CSA Certified	Yes
---------------	-----

**Dimensions**

Height	10.3
Depth	3.3
Width	6.4
Weight	5

## Publications

Title	Publication No.	Publication Type
<a href="#">General Duty Safety Switches: 30-600 Amp, 240 Vac</a> 1 page. For residential and light commercial applications.	DEE-576	Brochures
<a href="#">60A - Safety Switches</a> 1 page outline drawing in .pdf format.	10103091-SH104	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.