



BURNDY Catalog Number
UPC Number
Description
Status

GG181
 7818102600677
 1 BRAID TO 2 IPS
 Active

Web Use
 BURNDY Product Line

Dimensional

Width (in)	3.69
Height (in)	4.25
Size (Hex) or Size (Bolt)	3/8
Braid Max Width (in)	1.00
Braid Max Width (Fraction)	1
Size (Hex) or Size (Bolt) - in	0.38
B Length (in)	1.38
Width (Fraction)	3-3/4
Height (Fraction) (in)	4-1/4

General

Product Description Mechanical Grounding Connector, Copper Bar/Strap/Braid/Cable to Rod/Tube, 2" Pipe, 2"-2-3/8" Rod

Conductor(s)

Copper Tube Size (SCH40) - Range 2-2-1/4
 Rod Size (Range) 2 in

Physical

Installation Torque 240
 Type of Plating Unplated
 Plated (Yes or No) N
 Product Material Copper Alloy
 Screw Material Type DURIUM® Silicon Bronze

Approvals / Certifications

UL Listed N
 CSA Certified Y
 ROHS Compatible Exempt
 UL Recognized N
 CULUS N
 Industry Standards UL467
 Rated for Direct Burial Y

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175