

## FLEXIBLE AND PORTABLE CORD

Type GGC

90°C - 2000 Volt - UL



CONSTRUCTION	
Conductor	• Fully annealed Stranded Bare copper, ropelay stranding for maximum flexibility
Insulation	• EPDM for use up to 90°C
Jacket	• Heavy duty thermoset CPE

### Applications:

- Mining equipment, cranes, conveyors, and mobile equipment
- Excellent impact resistance
- Withstands severe environmental conditions
- Resistant to heat, acids, oil, moisture, and most chemicals

### Standards:

- ICEA 5-75-381
- MSHA Approved

COLOR CODE CHART	
Cond. #	Color
1	Black
2	White
3	Red

Part #	AWG	Conductors	Stranding	Ground Check AWG	Ground AWG	Nom. O.D.	Lbs./M'
B60803	8	3	49	10	2 # 10	.965"	600
B60603	6	3	65	10	2 # 10	1.02"	770
B60403	4	3	103	10	2 # 8	1.125"	1005
B60203	2	3	133	10	2 # 7	1.315"	1480
B60103	1	3	201	8	2 # 6	1.445"	1815
B61/003	1/0	3	259	8	2 # 5	1.57"	2205
B62/003	2/0	3	259	8	2 # 4	1.66"	2545
B63/003	3/0	3	420	8	2 # 3	1.81"	3230
B64/003	4/0	3	516	8	2 # 2	1.92"	3675
B625003	250	3	608	8	2 # 2	2.39"	5390
B635003	350	3	855	8	2 # 1/0	2.68"	7400
B650003	500	3	1235	8	2 # 2/0	3.03"	10100

\*Fittings are available for these products.

Note: The information in this specification sheet is approximate and subject to standard industry and manufacturer tolerances. Please verify specific requirements with your Omni Cable account manager.