



On Line Catalog



BURNDY Catalog Number
UPC Number
Description
Status

BIBD42
 7818102238199
 14-4 TWO SIDED UNITAP
 Active

Web Use
 BURNDY Product Line

Screw Size	1/4
Width (in)	1.50
Hex Size (Key)	1/8
Length (in)	1.08
Height (in)	1.25

Dimensional

Min Voltage Rating

Electrical
 600

Number of Ports
 Number of Screws

General

2
 2
 Aluminum Multiple Tap
 Connector, Clear Insulated, 2 Port,
 2 Sided Entry, 14-4 AWG, Al/Cu
 Rated

Product Description

Aluminum Size (Range)
 Copper Solid Size (Range)
 Copper Stranded (Range)

Conductor(s)
 8 AWG-4 AWG
 N/A
 14 AWG-4 Str

Type of Hardware
 Type of Plating
 Insulation Type
 Plated (Yes or No)
 Product Material

Physical

Aluminum
 Unplated
 Plastisol
 N
 Aluminum

UL Listed
 CSA Certified
 Rated for Direct Burial
 ROHS Compatible
 UL Recognized
 CULUS
 Industry Standards

Approvals / Certifications

Y
 Y
 N
 Compliant
 N
 N
 UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175