



# Carlon®

## Rigid Non-Metallic Conduit Bodies & Covers T&B Catalog Number:

E986D

**UPC Number:**

03448120749

**Status:**

Active

**Description:**

Type LB Conduit Body, Volume 4 Cubic Inches, Size 1/2 Inch, Length 3-7/32 Inches, Width 1-11/32 Inches, Material PVC, Color Gray, For use with Schedule 40 and 80 Conduit

### Features

Textured lids

Foam-in-place gasket

### Application

For use with Rigid Conduit

### General

Trade Size (inches)

1/2

Material

Non-Metallic

Volume (cu.in.)

4

Conduit Body Shape

LB

### Dimension Information

C (inches)

11/16

H (inches)

1 5/16

L1 (inches)

4 5/16

L2 (inches)

3 7/32

L3 (inches)

3 1/16

Q (inches)

1 11/32

W (inches)

1 1/2

### Packaging

Package in Units

25

T&B Sold in UOM

Each

T&B Weight Per UOM

17.5 lbs. per 100

### Application Support

T&B Sales Drawings

wsd-ac05071

Rigid Non-metallic Conduit Bodies

Available on Website

Specifications & Applications

Available on Website

### Certifications

RoHS Compliance

Yes

### Certifications



File Nbr:


E11461

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.

T&B Technical Support  
MS 3B-50

Hours: 7AM - 6PM CDT  
Monday-Friday



Memphis, TN 38125  
www.tnb.com

8155 T&B Blvd.  
Memphis, TN 38125

Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com