



*max overall height

Measurements:

Height

5.00"

Max OAH

52.50"

Hanging Weight

2.40 lb

Width

6.50"

Min OAH

10.50"

Lamping:

Incandescent MB Incandescent

1.00 100W MB Incandescent

100 total watt

Dimmable : Standard

1,150 Rated Lumens

Color Temperature

2,500 Rated Life

Shipping:

Carton Weight

3.30 lb

Carton Width

9.33"

Carton Height

6.30"

Carton Length

14.40"

Master Pack Qty

1.0000

UPC

783209012783

UPS

Yes

Finish:

Satin Nickel SN

Glass:

Marble MR

Material:

Steel

Certification:

Dry Location
Location

Additional:

MB Incandescent (Not Included)
Slope: 120