



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Definite Purpose Control - Contactor

**C25FNF260A**

**UPC:** 782113476100

**Dimensions:** 3.97 IN \* 2.63 IN \* 3.75 IN (L \* W \* H)

**Notes:** Resistive Load rating per pole

**Warranty:** 1 year

### Specifications:

- **Connection:** Quick
- **Amperage Rating:** 60A
- **Coil:** 110-120 Vac, 50/60 Hz
- **Enclosure:** Open with metal mounting plate
- **Frame Size:** 60-75A, two- and three-pole
- **Model:** Contactor
- **Number Of Poles:** Two-pole
- **Resistive Load:** 75A
- **Terminals:** Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)
- **Type:** Non-reversing

### Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [C25FNF2 3D Model Xchange](#)
- [Drawing Dataset](#)
- [C25FNF2 AutoCAD 2D Footprint](#)
- [C25FNF2 2D PDF](#)
- [C25FNF2 AutoCAD 2D Footprint \(mm\)](#)
- [C25FNF2 3D Inventor](#)
- [C25FNF2 2D Drawing Xchange](#)
- [Eaton Specification Sheet - C25FNF260A](#)

**Certifications:** No Data

**Product compliance:** No Data



