



Liquidtight Flexible Non-Metallic Conduit & Fittings

T&B Catalog Number:

15010-150

UPC Number:

03448123342

Status:

Active

Description:

1-1/2 Inch Gray Liquidtight Flexible Non-metallic Conduit, 150 Foot Reel

Features

Non-conductive and non-corrosive.

Lightweight for easy handling, transportation and installation.

Crush, abrasion and strain resistant.

Provides superior wire protection

Smooth interior ideal for pulling cable, no jagged edges.

Maintains internal I.D. even in tight radius bends.

Resistant to oil, acid, ozone, and alkaline.

UL listed for outdoor use and sunlight resistant.

UL listed for use as indicated in Article 356.2 of the NEC and Section 12-1300 of the Canadian Electrical Code, Part 1.

Suitable for use at conduit temperatures of 80 degree C dry, 60 degree C wet and 60 degree C oil resistant as required by Section 15-6 of ANSI/NFPA 79 and UL 1660.

Sequentially market footage

Application

Control and Motor

Air conditioning and heating

Computer power distribution

Machine Tools

Console wiring

Transformer connections

Outdoor lighting

General

Material Non-Metallic

Color Gray

Reel Length (feet) 150

Dimension Information

Size (inches) 1 1/2

Average O.D. (inches) 1.882

Average I.D. (inches) 1.58

Nominal Size (inches) 1 1/2

Packaging

T&B Order Multiple 150

Package in Units 150

T&B Sold in UOM Feet

T&B Weight Per UOM 0.69 lbs. Each

Application Support

Product Overview-Carflex Liquidtight Flex-Available on Website
ible Tubing

Notes

Available in black and gray.

Customer cut lengths available.

Certifications

RoHS Compliance

Yes

Certifications



File Nbr:

E95745

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com