



CUTTER,CABLE-RATCHET

Ratchet Cable Cutter (1.5 lbs/.7 kg)

Cat No: 45206

UPC No: 783310452065

### Description

---

- Simple, one-hand operation
- Exclusive two-speed ratcheting mechanism adjusts for light/heavy cutting
- Well-suited for tight working spaces
- Blades can be opened mid-cycle
- Available with cushioned handles or with 1000V insulated cushioned handles

### Specifications

---

- Application : For Tight Working Spaces
- Cutting Capacity Of Aluminum : 600.000 KCMIL (MCM) (300.000 SQ-MM) Maximum Use, 500.000 KCMIL (MCM) (240.000 SQ-MM) Frequent Use
- Cutting Capacity Of Communication Cables : 1-3/8 IN (35.000 MM) Diameter Frequent Use
- Cutting Capacity Of Copper : 600 KCMIL (MCM) (300.000 SQ-MM) Maximum Use, 500 KCMIL (MCM) (240.000 SQ-MM) Frequent Use
- Handle Type : Cushioned Grip
- Jaw Size : 1-7/16 IN (36.500 MM)
- Overall Length : 10.000 IN (254.000 MM)
- Replacement Part : 45218 Movable Blade, 45212 Fixed Blade And Handle
- Type : Ratchet
- Weight : 1.500 LB (0.700 KG)