



Actual

**Catalog Number:** UB7FN  
**Product ID:** 7TAA231120R0030  
**UPC Number:** 03448119495  
**Status:** Active

Schedule 80 Elbow, Size 4 Inches, Bend Radius 36 Inches, Bend Angle 45 Degrees, Material PVC

### North American Specifications (UNSPSC)

UNSPSC	39131717 Electrical conduit elbow
IGCC	5752 Pvc Schedule 80 Elbows
Brand Name	Carlton
Type	Rigid Non-Metallic Conduit-Schedule 80 Elbows
Standard	UL E323335
Trade Size	4 Inches
Material	PVC
Color	Gray
Length	33.57 Inches
Outside Diameter	4.5 Inches

### European Specifications (ETIM)

ETIM	EC001493 Bend for cable protection tubes
Material	Plastic
Material quality	PVC
Surface polished	N
Colour	Other
Model	Rigid
Shape	Outer - and inner side plain
Angle of bow	45°

### Packaging

Outer Quantity	1
Outer Dimensions (inches)	1x1x1
Weight Uom	8.45 lbs. Each

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)