

## FLEXIBLE AND PORTABLE CORD

**Type W -MultiConductor**  
**600 Volt to 2000 Volt**  
**90C -UL**



CONSTRUCTION	
Conductor	- Fully annealed Stranded Bare copper
Insulation	- EPR for use to 90C
Jacket	- thermoset CPE

### Applications:

- Mining equipment, cranes, conveyors, and mobile equipment
- Excellent impact resistance
- Withstands severe environmental conditions
- Resistant to heat, acids, oil, moisture, and most chemicals

### Standards:

- ICEA S-75-381/NEMA WC-58
- UL Type W
- MSHA Approved
- Sunlight Resistant

COLOR CODE CHART	
Cond. #	Color
1	Black
2	White
3	Green
4	Red
5	Orange

Part #	AWG	Conductors	Stranding	Insulation Thickness	Nom. O.D.	Lbs./M'
B50805	8	5	133	.060"	1.03"	650
B50605	6	5	259	.060"	1.17"	915
B50405	4	5	259	.060"	1.36"	1320
B50205	2	5	259	.080"	1.595"	1925
B50105	1	5	259	.080"	1.895"	2541
B51/005	1/0	5	259	.080"	1.900"	2885
B52/005	2/0	5	259	.080"	2.060"	3630
B53/005	3/0	5	420	.080"	2.260"	4900
B54/005	4/0	5	516	.080"	2.425"	5980

\*Fittings are available for these products.

Note: The data shown are approximate and subject to standard industry and manufacturer tolerances.