




WELDED GANG BOXES WITH CONDUIT KO'S

Gang Boxes, 1-5/8 in. Deep - Welded with Conduit KO's
3-Gang

A54



Catalog #: 952

APPLICATIONS

RACO® Gang boxes are used where a number of wiring devices are to be centrally located
N/A

PRODUCT FEATURES

- Gang boxes save time in installation, no need to gang boxes together
- Have 1/2" and 3/4" concentric KO's for use with a wide variety of wiring methods
- Bottom KO pattern, 3-1/2" and 2-3/4" at either end of box
- Accepts two styles of covers, flat and 3/4" raised device cover
- Use low voltage partitions #947 or #949

UL LISTED

File E195978

COMPLIANCES

MSDS
www.hubbell-rtb.com/certifications/Hubbell-RACO_MSDS_for_Steel_Boxes_and_Covers.pdf

GENERAL PRODUCT INFORMATION

Wiring System: Conduit

CONFIGURATION

Top & Bottom Knockouts(s): (10) 1/2-3/4 in. Concentric
 Back Knockout(s): (6) 1/2 in. & (4) 3/4 in.
 Gangs: 3
 Side Knockout(s): (4) 1/2-3/4 in. Concentric

DRAWING DIMENSIONS

Dimension A: 1-5/8 in.
 Dimension B: 8-13/16 in.
 Dimension C: 8-5/8 in.

PRODUCT MEASUREMENTS

Depth: 1-5/8 in.
 Cubic Inches (cm3): 60.0 (983.2)
 Wt. Ea. (Lbs.): 1.550
 Product Length (in.): 1.63
 Product Width (in.): 4.50
 Product Height (in.): 8.63

PACKAGING

Minimum Pack Qty.: 5
 Std. Pkg.: 5
 Product UPC-A Labeled: Yes
 Weight (Lbs. Per/C): 155.00
 Ship Carton Length (in.): 11.50
 Ship Carton Width (in.): 5.00
 Ship Carton Height (in.): 9.25
 Ctn Weight (Lbs.): 7.75
 Pallet Qty: 720
 UPC Number: 050169009529
 I2of5: 50050169009524