



Image File Name:
F601-BS-
BN_0.jpg

Item #: F601-BS/BN	UPC Code: 706411000003
Product Family Name: Acero™	Finish: Brushed Steel/Brushed Nickel
Category: Interior Fan	Category Type: Ceiling Fan
Certification E75795	
Patents U.S. Patent(s): 6,354,801; 6,517,316	
Notes:	



MEASUREMENTS

Blade Finish:	Reversible Blades:	
	No	
Blade Material:	Slope:	
ABS Construction	No	
Blade Sweep:	No. of Blades:	Blade Pitch:
52	3	14 degrees
Downrod 1:	Downrod 2:	Hanging Weight:
3.5	6	24.25
Ceiling to Lowest Point: (Dim A)	Downrod 1 Outside Dia:	Downrod 2 Outside Dia:
13.75	.75	.75
Ceiling to Blade: (Dim B)	Lead Wire:	Motor Size:
11.50	80	188x15mm

	Low:	Low/Med:	Medium:	Med/High:	High:
RPM:	74		113		183
Amps:	0.34		0.46		0.59
Watts:	15.000		32.000		70.000
CFM:	2500.00		4500.00		6500.00
CFM/Watts:	166.67		140.63		92.86



FAN CONTROLS

Pull Chain Control: No	Works with Remote Control: Yes	Works with Wall Control: Yes
	Included Remote Control:	Included Wall Control: WCS212
	Compatible Remote Control[s]: RCS212	Compatible Wall Control[s]:

LAMPING

No. of Bulbs: 1	Light Type: T4(E11) Mini Cand Halogen Frosted			
Max Bulb Wattage: 100	Socket: E11 Mini Cand			
Light Kit: Yes	Dimmable: Yes	Ballast:	Rated Life Hours:	Uplight:
Lamp Included: Yes	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:

GLASS

Description:	Material: Glass
Part No.: GF601	Quantity: 1
Width:	Height:
	Length:



SHIPPING

Carton Width: 15.000	Carton Height: 10.250	Carton Length: 27.250
Carton Weight: 26.400	Carton Cubit Feet: 2.425	Small Package Shippable: Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack: 1
		Master Pack: 1



Title 17

UL Listed

Yes

Yes