


TWO LAMP STRIP SERIES

Standard grade open channel available in one, two or four lamp combinations. Luminaires come in 2', 3', 4', 6' and 8' lengths featuring rapid start or slimline lamps in both T12 and T8 configurations. Multiple reflector choices combined with ease of installation make these units ideal for areas that require industrial application.



Dimensional Data



Specifications

Mounting: Fixtures may be surface or pendant mounted or in continuous rows. When mounting in rows turn end cap ninety degrees for joiner strap.

Construction: Housings die-formed of heavy gauge steel designed for maximum strength and uniformity. Wiring components are mounted in the one piece back housing, permitting the removal of the cover for maintenance or cleaning without disturbing any of the inner wiring.

Finish: All metal parts are thoroughly cleaned and treated to prevent rust and deterioration with a phosphate coating. Surfaces are then electrostatically sprayed with a high quality white enamel with a minimum reflectance of 87%.

Wiring: Standard ballast are universal voltage (UV).

Approval: All units are Underwriters' Laboratories (UL) approved.

Ordering Information

Catalog #	Lamps	Length	Catalog #	Lamps	Lengths	Catalog #	Lamps	Lengths
ELECTRONIC OCTRON T8								
1 Lamp			2 Lamp			4 Lamp		
S140WEBO	1-F32T8	4'	S220EBO	2-F17T8	2'	S440EBO	4-F32T8	4'
S130TWEBO	2-F25T8	6'	S230EBO	2-F25T8	3'	S496EBO	4-F96T8	8'
S196EBO	1-F96T8	8'	S240EBO	2-F32T8	4'			
S196TEBO	2-F96T8	16'	S240TEBO	4-F32T8	8'			
			S230TEBO	4-F25T8	6'			
			S296EBO	2-F96T8	8'			
								ALSO AVAILABLE IN T5

Photometrics:

Photometric Information available upon request.




TWO LAMP STRIP SERIES

Options and Accessories *Add Suffix*

EB	Electronic T12
*CW	(Note 1,2) Low Temperature (0) Ballast
*DIM	Dimming Ballast
EM	Emergency Ballast (1 lamp)
•EM/2	Emergency Ballast (2 lamp)
RFI	Radio Interference Filter
FS	External Fuse and Holder
CORD-3W	6' 3 Wire Cord and Plug
REF	Internal Polished Aluminum Reflector
REFS	Internal Specular Silver Reflector

* Available Electronic T12 or Electronic T8.
 note 1: Slimline Electronic T8 0 degrees Standard.
 •Note: Consult Factory on Compatibility EM/2 Option.

Installation Data



Reflector Data

