



61952-962: One Light Mini-Pendant



Dimensions:

Diameter: 6 1/2" **Overall Height:** 55 1/4"
Height: 8 1/2" **Wire:** 120"
Weight: 4.1 lbs. **Mounting Proc.:** Screw Collar - Stem
Connection: Mounted To Box

Bulbs:

1 - Medium A19 60w Max. 120v - Not included
 1 - LED Medium A19 8w Max. 120v - Not included
 1 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- Easily converts to LED with optional replacement lamps
- Sloped ceiling mounting hardware included
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

Collection: Stirling

One Light Mini Pendant in Brushed Nickel Finish with a White Linen Shade.

Includes three interconnecting 12" stems and one 6" stem

UPC #: 785652027413

Finish: Brushed Nickel (962)

Material List:

1 Body - Steel - Brushed Nickel
 2 12" Stem - Steel - Brushed Nickel
 1 6" Stem - Steel - Brushed Nickel

Safety Listing:

Safety Listed for Dry Locations
 Safety Listed for Dry Locations

Instruction Sheets:

Trilingual (English, Spanish, and French) (HC-1728FS)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Fabric	White Linen	1				6 3/8	6 1/2	1 5/8			
Diffuser	Glass	Satin Etched	1				1/8	5 1/2	1 5/8			

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	1 3/8			5 1/2		

Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	61952-962	1	785652027413	17	9.25	13	1.183	5.1	150	Yes

NJ Pallet		80		48	40	77	85.556	306		No
NV Pallet		60		48	40	77	85.556	306		No