

**Search Parameters:**

e-Catalog > [Circuit Breakers](#) > Molded Case Circuit Breakers  
**Circuit Breakers, Molded Case Circuit Breakers**

Product #: TEY330ST12

Short Description: MCCB 3P 30A W/120-277VAC SHUNT TRIP

**SPECIFICATIONS**

Category	Lighting Panel Circuit Breakers
Product Line	TEY / Q-Line (Bolt-On)
Trip Style	Non-Interchangeable
Amperage	30A
Poles	3
System Voltage	120 Vac , 120/240 Vac , 240 Vac , 277 Vac
120 Vac Interrupting Rating	65 KAIC
120/240 Vac Interrupting Rating	65 KAIC
240 Vac Interrupting Rating	65 KAIC
277 Vac Interrupting Rating	14 KAIC
Trip Function	LI
Continuous Current Rated	Standard
Suitable for Reverse Feed	Yes
Long Time	Fixed
Instantaneous	Fixed
Current Metering	No
Protective Relays	No
Special Markings	HACR , HID
Wire Range (Cu/Al)	14-8 kcmil / 12-8 kcmil
UL File #	E11592
CSA File#	LR57114
GSA Compliance	No
GO Schedule	EY
UPC	078316419663
List Price	\$1011



[View Larger](#)

**Publications/Resources**

[TEY330ST12](#)

**Additional Resources for Lighting Panel Circuit Breakers**

- [Application and Technical Brochures](#)
- [Drawings-Outline and Dimensional Installation and Instruction](#)
- [Time Current Curves](#)

The TEY is a one-inch wide per pole, compact, "bolt-on" circuit breaker for use on grounded 480Y/277 Vac systems. The bolt-on mounting base accessory makes the TEY suitable for varied applications as a lug-lug breaker. All TEY circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. TEY breakers are available in 1, 2, and 3 pole versions and can be ordered with auxiliary contact and shunt trip accessories.

**Products**

- [Critical Power](#)
- [Drives and Controls](#)
- [Electrical Distribution](#)
- [New Products](#)

**Services**

- [Aftermarket Solutions](#)
- [Arc Flash Services](#)
- [Critical Power Services](#)
- [Drives Services](#)
- [Emergency Services](#)
- [Engineering Services](#)
- [Hydro Services](#)
- [Industrial Service Centers](#)
- [Inspection Services](#)
- [Mechanical Services](#)
- [Motor Services](#)
- [Power Delivery Services](#)
- [Product Registration](#)
- [Training](#)
- [Transformer Services](#)

**Markets**

- [Commercial](#)
- [Data Center](#)
- [Health Care](#)
- [Industrial](#)
- [Mining](#)
- [Oil & Gas](#)
- [Telecom](#)

**Resources**

- [Publication Library](#)
- [Project Assistant 2.0](#)
- [Videos](#)
- [Social Media & Apps](#)
- [Data Visualization](#)
- [Counterfeit Beat](#)
- [Newsletter Subscriptions](#)
- [e-Catalog](#)
- [GE Smart Catalog](#)
- [BuyLog](#)
- [Control Catalog](#)
- [Embedded Power Guide](#)
- [Tools & Calculators](#)

**Your Business**

- [Contractor](#)
- [Distributor](#)
- [Electrical Maintenance Org.](#)
- [Facilities Operations](#)
- [Original Equipment Mfr.](#)
- [Consulting / Design Engineer](#)

**News & Events**

[Where To Buy](#)

**Industrial Solutions**

Industrial Solutions, a GE heritage business, is leading the future of electrification with advanced technologies that distribute, protect and control. We provide customers, across various industries, with end-to-end product and service solutions that ensure the reliability and protection of the electrical infrastructure; from the power station to the end point and the sustainable power technologies in between.

[ABOUT US](#)

[CONTACT INFORMATION](#)

[PRIVACY](#)

[TERMS OF USE](#)



WORLDWIDE PARTNER