

X7899-HGI

Tamper Resistant Receptacles



UPC Code: 07847760148

Country of Origin: China

Brand Features

Slim is in. New SmartlockPro Slim GFCIs Install Easily Industry-leading quality, professional grade lockout action, and the slimmest profile on the market make SmartlockPro Slim GFCIs the smartest choice in ground fault circuit interrupter protection. Faster and easier to install in any wallbox because depth is reduced, the slim GFCIs flush mount to the wall with minimal protrusion for a sleek, finished look. Enhanced features include external back wiring for positive indication the wire is properly seated, exceptional resistance to wire pullout and the ability to withstand high torque. Tamper-Resistant to meet 2008 NEC Requirements for new or renovated residential construction.

Item Description

20 Amp, 125 Volt Receptacle, Hospital Grade, 20 Amp Feed-Through, Tamper-Resistant, SmartlockPro Slim GFCI, Monochromatic, back and side wired, nylon wallplate, screws and self grounding clip included - Ivory

Technical Information

AC Horsepower Ratings

At Rated Voltage: 1 HP

Electrical Specifications

Amperage: 20 Amp

Voltage: 125 Volt

NEMA: 5-20R

Pole: 2

Wire: 3

Frequency (Hertz): 60

Short Circuit Current Rating: 10kA

Feed-Through Current: 20 Amp

Environmental Specifications

Flammability: Rated V-0 per UL94

Operating Temperature: -35C to +66C

Material Specifications

Face Material: PBT

Body Material: Polycarbonate

Terminal Screws: Plated Steel

Grounding Screw: Plated Steel

Clamps: Brass

Strap Material: Galvanized Steel

Shutter Mechanism: Delrin® Acetal

Mechanical Specifications

Terminal Accom.: 14-10 AWG

Product ID: Ratings permanently marked on device

Performance Data

Trip Level: Class A, 5mA plus or minus 1mA

Diagnostics: LED

Product Features

Feature: Tamper-Resistant

Color: Ivory

Standards and Certifications

NEMA: WD-1 & WD-6

ANSI: C-73

UL 498: File E13399

CSA C22.2 No. 42: File LR-57811

NOM: 057

UL 943: File E48380

UL Fed Spec WC-596: Yes

Warranty

Warranty: 2 Year Limited

SPECIFICATION SUBMITTAL

JOB NAME:	CATALOG NUMBERS:	
<input type="text"/>	<input type="text"/>	<input type="text"/>
JOB NUMBER:	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Telephone: 1-800-323-8920 · FAX: 1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): 1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: 1-800-469-7890 ·

FAX: 1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2012-2016 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to: www.leviton.com/international/contacts/

