



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## CH 3/4-inch loadcenter

CH30B3200R

UPC:782113097992

### Dimensions:

- **Height:** 5.19 IN
- **Length:** 39 IN
- **Width:** 14.31 IN

**Notes:**Furnished with hub closure plates.

### Warranties:

- Limited lifetime

### Specifications:

- **Special Features:** Standard
- **Type:** Main breaker
- **Amperage Rating:** 200A
- **Box Size:** L
- **Bus Material:** Copper
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 10 kAIC
- **Main Circuit Breaker:** CC
- **Number Of Circuits:** 30
- **Number Of Wires:** Four-wire
- **Phase:** Three-phase
- **Wire Size:** #2/0 AWG-300 kcmil
- **Feed Type:** Overhead

### Supporting documents:

- [Dimensional Drawing - CH 3/4 LOADCENTER, CC MAIN BREAKER, OUTDOOR NEMA 3R, 120/240 VAC, 3 PH](#)
- [Type CH Circuit Breakers and Loadcenters](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)



- [Eaton Specification Sheet - CH30B3200R](#)

**Certifications:**

- UL 50
- UL 67

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.