



Item #: **F711-PW**
 Product Family Name: **Delano® II**
 Category: **Interior Fan**
 Certification: **E75795**
 Patents: U.S. Patent(s): D595,403; D597,655
 Notes:

UPC Code: **706411034626**
 Finish: **Pewter**
 Category Type: **Ceiling Fan**



Image File Name:
 F711-PW--
 1378920357.jpg



MEASUREMENTS

Blade Finish:	Reversible Blades:		
	No		
Blade Material:	Slope:		
Plywood Construction	No		
Blade Sweep:	No. of Blades:	Blade Pitch:	Hanging Weight:
52	5	14 degrees	24.80
Downrod 1:	Downrod 1 Outside Dia:	Downrod 2:	Downrod 2 Outside Dia:
Ceiling to Lowest Point: (Dim A)	Ceiling to Blade: (Dim B)	Lead Wire:	Motor Size:
11.75	8.00	8	172*20mm

	Low:	Low/Med:	Medium:	Med/High:	High:
RPM:	68		115		150
Amps:	0.34		0.51		0.58
Watts:	17.000		43.000		70.000
CFM:	1976.00		3899.00		5634.00
CFM/Watts:	116.24		90.67		80.49



FAN CONTROLS

Pull Chain Control:	Works with Remote Control:	Works with Wall Control:
No	Yes	Yes
	Included Remote Control:	Included Wall Control:
		WCS212
	Compatible Remote Control[s]:	Compatible Wall Control[s]:
	RCS212	

LAMPING

No. of Bulbs:	Light Type:			
2	T4(E11) Mini Cand Halogen Clear			
Max Bulb Wattage:	Socket:			
50	E11 Mini Cand			
Light Kit:	Dimmable:	Ballast:	Rated Life Hours:	Uplight
Yes	Yes			
Lamp Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
Yes				

GLASS

Description:	Material:
	Glass
Part No.:	Quantity:
GF711	1
Width:	Height:
	Length:



SHIPPING

Carton Width:	Carton Height:	Carton Length:	
16.000	10.250	27.500	
Carton Weight:	Carton Cubit Feet:	Small Package Shippable:	
28.360	2.610	Yes	
Master Pack Width:	Master Pack Height:	Master Pack Length:	
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:	Master Pack:
			1



Title 17

Yes



UL Listed

Yes