



98061-12: 100w 12V Zero-Load LED Tape Transformer **Dimensions:**

Length:	5"
Width:	2"
Height:	1"



Material List:

Safety Listing:

cETL Listed for Dry Locations

Instruction Sheets:

Trilingual (English, Spanish, and French) (HC-1844FS)

Collections: Transformers (Primary)
Ambiance LED Under Cabinet

Hardwire 100w 12V zero load electronic transformer for Ambiance LED Tape. Features an integral 5-pin female connector for direct connection with the first LED tape strip in your run. Maximum run length of 20 feet on 12V. Ambiance electronic transformers have soft start circuitry which increases lamp life. They emit no audible noise, are UL and C-UL approved, moisture and shock resistant, employ automatically resetting short circuit protection, and are dimmable using an electronic low-voltage (ELV) dimmer.

UL 2108 approved, flame resistant plastic cases with wiring compartment & integrated strain relief (input side).

Low profile design that mounts neatly out of view (1"H x 1.6"W x 5"L)

Compatible with most standard dimmers including electronic low voltage dimmers (recommended)

Electronic circuit design for increased efficiency & reliability

Short circuit & overload protection, automatic shut down/reset

Emits no audible noise, sound rated A

Maximum operating temperatures -20°C to +90°C

Input 120VAC, output 12VAC 0-100W

High power factor > 95%

ETL listed, dry location

New/improved transformer case/enclosure: An electrically isolated, flame resistant, UL 2108 approved plastic enclosure

UPC #:785652159428

Finish: Black (12)

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	98061-12	1	785652159428	9	4	4	0.083	0.8	85	Yes
Master Pack	98061-12	6	10785652159425	8.75	7.25	6.25	0.229	5.3	85	Yes
Shipping Master		24	20785652159422	18.75	15.5	8	1.345	22.9	85	Yes
NJ Pallet		1296		48	40	77	85.556	1236.6		No