


5" Aperture, Lytning, Incandescent, Convertible IC/Non-IC, Frame-In Kit

Project:	Catalog No:	Mfg:
Location:	Fixture Type:	Qty:
Notes:		Lamps:



5" Aperture: Complete Fixture consists of Reflector Trim & Frame-In Kit. Select each separately.

Frame-In Kit	Description	Open Downlight						Adjustable	Enclosed Diffusers	Open Wet Location	Wall Washer
		Anodized Reflector	Anodized Cone		Satin Cone	Baffles	Basic White				
1004IC	FIK	1045	1012	1012NM	1008	1005	1071	1022	1021*	1081CD	1085*
1004ICN	FIK with Nails	1046	1013	1013NM	1008NM	1005NM		1022WH	1024*	1081WH	
1004ICQ**	FIK with Quick Connect	1046CD	1013BK	1013BKNM	1010	1005WH		1082	1177LX		
1004ICNQ**	FIK with Quick Connect		1013CD	1013CDNM	1010NM	1005BNM		1088	1178LX		
			1013WH			1076		1088GW	1090*		
						1076WH		1088WH			

* For Non-IC applications only.
 ** Supplied with integral push-in wire connectors

Features

- Housing:** .032 (#20 ga.) aluminum. UL listed convertible IC/NON-IC. 2" vertical adjustment in ceiling. Can be removed for access to junction box and ceiling plenum. AirSeal® housing minimizes air leakage to less than 2 CFM at 1.57 PSF (or 75pa), which complies with Model Energy Code (Section 602.3.3) and Washington State Energy Code (Section 502.4) and reduces heat loss and condensation in ceiling.
- Mounting Frame:** .048 (#18 ga.) galvanized steel. Locks into position along length of mounting bars with locking spring and bendable slot. (3) slots 90° apart simplify alignment.
- Junction Box:** 2" X 4" X 3 1/2" (22 cu. in.) .032 (#22 ga.) galvanized steel. UL listed. AC only, min 90° supply conductors suitable for branch circuit wiring supplying connected luminaires. AC only, min 90° supply conductors suitable for branch circuit wiring supplying connected luminaires. Cable clamp permits attachment of non-metallic (#12 or #14 ga.) Romex® cable without tools or additional connectors.
- Mounting Bars:** .059 (#16 ga.) galvanized steel. Bars pivot for easy attachment and wire-in below ceiling line. Bars extend to accommodate 16" to 24" O.C. joist spacing. The 1004IC features integral self-tapping philips screws for secure attachment to wood or metal construction. The 1004ICN features integral nails for secure attachment to wood. Both attach to T-bar ceilings without the need of accessories.
- Socket Housing:** Impact extruded aluminum or galvanized steel. Attached trim retaining spring secures trim to any height on housing wall.
- Socket:** Porcelain medium base: nickel plated screw shell. Pre-wired with #18 ga. SF1 (300 VOLT 200° C) leads to junction box.
- Thermal Protector:** Meets NEC and UL requirements. Located inside housing.

Options & Accessories

- AirSeal Kit: LAS56**
 NOTE: Use only if factory installed tape or knockouts are removed from vertical adjustment slots in housing wall.
- LED Retrofit Kit: LARFA**
 Allows use of 1076L and 1013L series LED Trims. See LARFA specification sheet for compatibility list.
- Labels**
 UL (Type IC/NON-IC Convertible; Suitable for Damp Locations)
 Complies with Air Leakage Requirements stated in the Model Energy Code and the Washington State Energy Code.

AirSeal is a registered trademark of Lightolier.
 Romex is a registered trademark of General Cable Industries Inc.