



Representative Image

Catalog No. TM4222CCU

Description: 225A 42CT 1P3W 120/240V 22K IC COMB

UPC No 783164112672

Home > Load Centers > Residential Load Centers > Single Phase - USA

PowerMark Gold 225 Amp 42-Space 42-Circuit Indoor Main Breaker Circuit Breaker Panel

- Indoor NEMA 1 Enclosure
- Main Breaker is Factory Installed
- Use with Equipment Ground Kit TGK42 (order separately)
- UL Listed (Panelboards No. 67)
- 60°/75°C Conductor Rating
- Suitable for use as service entrance equipment when Installed in accordance with the National Electrical Code
- 22kAIC RMS symmetrical, Except Where Noted
- 6-42 circuit devices UL Listed for bottom mounted lugs by installing complete unit (box, interior and front) upside down
- For a listing of CSA Listed load centers, visit www.geelectrical.com

Descriptors

Category	Single Phase - USA
GO Schedule	RD

Specifications

Input/Output Voltage	120/240V ac
Type	Standard
Interrupting Capacity Rating	22
Amperage	225 A
Device Type	Main Breaker
Enclosure	Indoor Type 1 Enclosure, Combination
UL/CUL Listing	UL
Phase	1 Phase
1" Space	42
1/2" Space	0
Feed	Either
Door	Yes
GSA Compliance	No

Publications

Title	Publication No.	Publication Type
Indoor Load Center 1 page outline drawing in pdf format.	10103091-SH24	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.