

InvisiLED® Pro


24V LED Tape Light

WAC LIGHTING

Responsible Lighting®



Tape Section



3 LED "L" Connector

Fixture Type:

Catalog Number:

Project:

Location:

PRODUCT DESCRIPTION

Professional grade white tape light that delivers optimal color consistency and brightness. An ideal system for task or accent lighting applications.

FEATURES

- Ultra thin profile at 3/8"
- Diodes spaced evenly at 1" on center
- Minimum run length of 1'
- May be field cut every 2" at the end of a run
- Three mounting methods provided for different surfaces
- Specially rated for installation in the storage area of a clothes closet
- 50,000 hour rated life
- 5 year WAC Lighting product warranty

SPECIFICATIONS

Construction: Flexible, silicone cased tape light. Peel and stick 3M construction adhesive on back. Indicating marks on back for field cutting.

Power Supply: Remote and plug-in electronic Class 2 transformers. 120VAC 50/60Hz input, 24V 60W and 96W output.

Light Source: 12 LEDs per foot


Dimming: May be dimmed with electronic low voltage (ELV) dimmer.

Operating Temp: -4°F – 122°F (-20°C – 50°C), relative humidity 95%.

Standards: UL & CUL Listed for damp locations.

ORDER NUMBER – TAPE SECTION

Model	Watts/ft	Color Temp	CRI	Lumens/ft	Length	Qty	Tape Color
LED-T24	3	W 2700K	85	200	2IN 2 inches	1	WT White
		P 3000K	85	200	2IN-10 2 inches	10	
		35 3500K	85	207	1 1 foot	1	
		1-40 1 foot	40				
		5 5 feet	1				




LED-T24___ - ___-WT

Example: **LED-T24P-2IN-10-WT**

ORDER NUMBER – 3 LED "L" CONNECTOR

Model	Watts	Color Temp	CRI	Lumens	Tape Color
LED-T24	1.2	W 2700K	85	50	3L-WT White
		P 3000K	85	50	
		35 3500K	85	52	
		C 4500K	85	54	



LED-T24___ -3L-WT

Example: **LED-T24C-3L-WT**

wacighting.com
Phone (800) 526.2588
Fax (800) 526.2585

Headquarters/Eastern Distribution Center
44 Harbor Park Drive
Port Washington, NY 11050

Central Distribution Center
1600 Distribution Ct
Lithia Springs, GA 30122

Western Distribution Center
1750 Archibald Avenue
Ontario, CA 91760




InvisiLED® Pro

24V LED Tape Light





















WAC LIGHTING

Responsible Lighting®

Class 2 Power Supply (Required)

Type	Model	Input	Output	Max Run	Dim		
Remote		EN-2460-RB2-T	120VAC	24VAC / 60W	20 feet	ELV	<i>Includes a 6 foot lead wire</i>
		EN-24100-RB2-T	120VAC	24VAC / 96W	33 feet	ELV	
Plug-in		EN-2460-P-AR-T	120VAC	24VAC / 60W	20 feet	ELV	<i>Includes a 6 foot lead wire</i>
		EN-24100-P-AR-T	120VAC	24VAC / 96W	33 feet	ELV	
Remote 277V		EN-24100-277-RB2-T	277VAC	24VDC / 96W	33 feet	0-10V	<i>Includes a 6 foot lead wire</i>

Accessories

Aluminum Channel		LED-T-CH	5 feet	<i>Includes a diffuser, two end caps, and five screws</i>				
Deep Aluminum Channel		LED-T-CH1	5 feet	<i>Includes a diffuser, two end caps, and five screws</i>				
45° Angled Aluminum Channel		LED-T-CH2	5 feet	<i>Includes a diffuser, two end caps, and ten screws</i>				
Fixed Angle Channel Clip		LED-T-CL3-PT	5 feet	<i>Used to mount any aluminum channel Includes 2 pieces, 4 screws</i>				
Adjustable Channel Clip		LED-T-CL2-PT	5 feet	<i>Used to mount any aluminum channel Adjusts 50° from center either way Includes 2 pieces, 4 screws</i>				
Retrofit Channel		LED-T-RC	3 feet	<i>Creates fixed curves</i>				
Clip		LED-T-CL	10 pcs	<i>Holds the tape from the underside Includes 10 pieces, 10 screws</i>				
Curve Clip		LED-T-CL1	10 pcs	<i>Runs over the tape to secure the angled tape Includes 2 pieces, 4 screws</i>				
Lead Wire		LED-TC-P-2	Black	2 ft	<i>Alternative lengths for plug-in power supplies</i>			
		LED-TC-P-2-WT	White	2 ft				
		LED-TC-P-12	Black	12 ft				
		LED-TC-P-12-WT	White	12 ft				
Extension Cable		LED-TC-EXT-144	Black	12 ft	<i>Extends distance between a hard wired power supply or wiring box to a tape section</i>			
		LED-TC-EXT-144-WT	White	12 ft				
Low Voltage Wiring Box With Feed		LED-TC-B-2	Black	L: 1½" W: ¾" H: 7/8"	<i>Neatly houses up to two wires with 12" female feed</i>			
		LED-TC-B-2-WT	White					
Low Voltage Wiring Box		LED-T-B	White	L: 1½" W: ¾" H: 7/8"	<i>Neatly houses up to two wires</i>			
Wiring Box With Switch		TB-S	White	L: 6¼" W: 1½" H: 1¼"	<i>Use when spanning a large gap in a system layout without leaving exposed wiring</i>			
Joiner Cable		LED-TC-IC2	Black		LED-TC-IC2-WT	White	2 in	<i>Connects tape sections</i>
		LED-TC-IC6	Black		LED-TC-IC6-WT	White	6 in	
		LED-TC-IC12	Black		LED-TC-IC12-WT	White	12 in	
		LED-TC-IC36	Black		LED-TC-IC36-WT	White	36 in	
		LED-TC-IC72	Black		LED-TC-IC72-WT	White	72 in	
3-Way "Y" Connector		LED-TC-Y	Black	<i>Connects tape sections</i>				
		LED-TC-Y-WT	White					
4-Way "X" Connector		LED-TC-X	Black	<i>Connects tape sections</i>				
		LED-TC-X-WT	White					
"L" Connector		LED-TC-L	Black	<i>Connects tape sections</i>				
		LED-TC-L-WT	White					
End cap		LED-TC-EC	Black	<i>1 cut end cap and 1 male end cap</i>				
		LED-TC-EC-WT	White					
Male to male connector		LED-TC-MM	Black	<i>50 Qty</i>				