

Item #: P472-084	UPC Code: 874944002570
Product Family Name:	Finish: BRUSHED NICKEL
Category: Wall Sconce	Category Type: Sconce
Certification E87611CCC	
Patents	
Notes:	



Image File Name:
P472-084--
1377187721.jpg



MEASUREMENTS

Width: 16	Length: 11	Height: 7	Extension: 7
Height Adjustable: No	Min Overall Height:	Max Overall Height:	Slope: No
Wire Length: 7	Chain Length:	Safety Cable Included: No	Net Weight: 2.20
Canopy Width: 5.00	Canopy Height: 5.00	Canopy Length:	
Backplate Width:	Backplate Height:	Center to Top: 8.50	Center to Bottom: 2.50

LAMPING

No. of Bulbs: 2	Light Type: A15 Med			
Max Bulb Wattage: 60	Socket: E26 Med			
Dimmable: Yes	Ballast:	Rated Life Hours:	Photocell Included:	Lamps Included: No
Lamp Included: No	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:

SHADE / GLASS

Description:	Material: Cloth
Part No.: RPE1607-1	Quantity:
Width: 6.75	Height: 16.00
	Length: 16.00



SHIPPING

Carton Width: 8.000	Carton Height: 9.500	Carton Length: 18.000
Carton Weight: 3.300	Carton Cubit Feet: 0.792	Small Package Shippable: Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack: 1
		Master Pack: 1



Damp Location
Yes



Title 17
Yes



UL LISTED
Yes