



BI-METAL SHIP AUGER BITS

TOUGHER THAN NAILS

EXTREME DURABILITY

High speed steel cutting edge for superior durability in nail-embedded wood

LONGER LIFE

High speed steel screw tip increases wear resistance for extended life

FAST, EASY DRILLING

Unique parabolic screw tip pulls the bit through material quickly and effortlessly

RESHARPENABLE

Resharpenable with LENOX Diamond File (product no. 25312)



SPECIFICATIONS

WARRANTY

SPECIFICATIONS

1 PER PACK	PRODUCT NO	HOLE DIAMETER		OVERALL LENGTH		TWIST LENGTH	
		IN	MM	IN	MM	IN	MM
14555	07A-1016	5/8	16	7-1/2	191	4	102
14556	07A-1116	11/16	18	7-1/2	191	4	102
14557	07A-1216	3/4	19	7-1/2	191	4	102
14558	07A-1316	13/16	21	7-1/2	191	4	102
14559	07A-1416	7/8	22	7-1/2	191	4	102
14560	07A-1516	15/16	24	7-1/2	191	4	102
14561	07A-1616	1	25	7-1/2	191	4	102
14562	07A-1716	1-1/16	27	7-1/2	191	4	102
14563	07A-1816	1-1/8	29	7-1/2	191	4	102
14564	07A-2016	1-1/4	32	7-1/2	191	4	102
14565	07A-2216	1-3/8	35	7-1/2	191	4	102
14566	07A-2416	1-1/2	38	7-1/2	191	4	102

1 PER PACK	PRODUCT NO	HOLE DIAMETER		OVERALL LENGTH		TWIST LENGTH	
		IN	MM	IN	MM	IN	MM
14539	008-0616*	3/8	10	18	457	12	305
14540	008-0716*	7/16	11	18	457	12	305
14541	008-0816	1/2	13	18	457	12	305
14542	008-0916	9/16	14	18	457	12	305
14543	008-1016	5/8	16	18	457	12	305
14544	008-1116	11/16	18	18	457	12	305
14545	008-1216	3/4	19	18	457	12	305
14546	008-1316	13/16	21	18	457	12	305
14547	008-1416	7/8	22	18	457	12	305
14548	008-1516	15/16	24	18	457	12	305
14549	008-1616	1	25	18	457	12	305
14550	008-1716	1-1/16	27	18	457	12	305
14551	008-1816	1-1/8	29	18	457	12	305
14552	008-2016	1-1/4	32	18	457	12	305
14553	008-2216	1-3/8	35	18	457	12	305
14554	008-2416	1-1/2	38	18	457	12	305

*3/8" shank—all others 1/2" shank.

RELATED PRODUCTS



BI-METAL UTILITY BIT

Tougher Than Nails

[Read more](#)



SELF-FEED WOOD BORING BIT

Designed for Rough -In Work

[Read more](#)

