



77262-962: Two Light Flush / Semi-Flush Convertible



Dimensions:

Diameter: 14" **Height Flush:** 12 3/4"
Height: 8 1/2" **Wire:** 6 1/2"
Weight: 3.3 lbs. **Mounting Proc.:** Cap Nuts
Connection: Mounted To Box

Bulbs:

2 - Medium A19 100w Max. 120v - Not included

Features:

- Can be installed semi-flush to ceiling or on fan
- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

Material List:

1 Body - Steel - Brushed Nickel

Safety Listing:

Safety Listed for Dry Locations

Instruction Sheets:

Trilingual (English, Spanish, and French) (990C77262-DYN)

Collection: Dayna Shade Pendants

Fixture is dual mount and can be installed as a flush mount or semi-flush mount light.

UPC #:785652222597

Finish: Brushed Nickel (962)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Fabric	Faux Silk	1				8 1/2	14				
Diffuser	Acrylic	White	1									

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	1			5		

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	77262-962	1	785652222597	15.5	15.58	12	1.677	5.9	250	Yes
NJ Pallet		46		48	40	77	85.556	271.4		No
NV Pallet		46		48	40	77	85.556	271.4		No