



Electrical Utility

[Products](#) | [Solutions](#) | [Documentation & Literature](#) | [News & Tradeshows](#) | [Support](#)

[United States](#) > [Energy](#) > [Electrical Utility](#) > [Products](#) > [Electrical Utility Products Catalog](#) > [Electrical Tape, Mastics & Special Use](#) > [Special Use Tapes](#) > [Scotch® Electrical Insulating Varnished Cambric Tape 2520, 3/4 in x 60 ft](#)

[Find An Account Rep](#)

[Where To Buy \(Find A Distributor\)](#)

[Contact Us](#)

Scotch® Electrical Insulating Varnished Cambric Tape 2520, 3/4 in x 60 ft

3M ID 80610989537 UPC# 00054007048367 Part Number 2520-3/4X60FT

[Print](#)



Scotch® Varnished Cambric Tape 2520 is straight-cut woven cotton cambric fabric, oil primed and coated with a high-grade yellow electrical insulating varnish. Flexible, moisture resistant with a smooth finish. Excellent dielectric strength with high puncture and cut-through resistance. Pressure-sensitive adhesive holds tape in position. Electrical properties stable up to 220°F (105°C). 8 mil.

- 3/4 in x 60 ft
- Straight-cut woven cotton cambric fabric, oil primed and coated with a high-grade yellow electrical insulating varnish
- Flexible, electrically insulating and moisture resistant with a smooth finish
- Excellent dielectric strength with high puncture and cut-through resistance
- Electrical properties stable up to 220°F (105°C)
- Pressure-sensitive adhesive holds tape in position after application
- 8 mil thickness
- For insulating bus bars, motor leads (for re-entry), and service drop connections
- Please review the Scotch® Varnished Cambric Tapes 2510 and 2520 data sheet carefully to ensure this product meets your application requirements.

Need Help? [ire](#)

Questions? We can help
[Contact Us](#)

Overview

Documents

Tape is used for insulating bus bars, motor leads (for re-entry), and service drop connections. NOTICE: straight weave cambric. Please review the Scotch® Varnished Cambric Tapes 2510 and 2520 data sheet carefully to ensure this product meets your application requirements.

Specifications

Adhesive Material	Rubber Resin
Agency Approvals	ASTM D-1000, ASTM D-374, ASTM D-295
Backing Material	Cotton Cloth
Breaking Strength	50 lb/in
Color	Yellow
Dielectric Strength	800 V/mil
Family	Scotch® Varnished Cambric Tape 2520
Length	60 Linear Foot
Material	Straight cut woven cotton cambric with electrical insulating varnish
Operating Temperature Range	Up to 105 Degree Celsius
Operating Temperature Range (Fahrenheit)	Up to 220 Degree Fahrenheit
Product Family	Scotch® Varnished Cambric Tape 2520
RoHS 2011/65/EU Compliant	Yes
RoHS EU Comments	RoHS 2011/65/EU compliant without exemption *Important RoHS information
Rolls per Carton	1

Rolls per Case	20
Specifications	ASTM D-1000, ASTM D-374, ASTM D-295
Tape Grade	Premium
Tape Type	Insulating and Splicing
Tensile Strength	6250 psi
Thickness	8 mil
Trademark	Scotch
Width	0.75 Inch

3M Electrical Utility: [Contact Us](#)

3M: [News](#) | [Careers](#) | [Partners & Suppliers](#) | [Investor Relations](#) | [SDS Search](#) | [Transport Information Search](#) | [Help Center](#)

[Legal Information](#) | [Privacy Policy](#)

© 3M 2017. All Rights Reserved.