



## Electrical Commercial and Industrial

[Products](#) | [Documentation & Literature](#) | [News & Tradeshows](#) | [Support](#)

[United States](#) > [Energy](#) > [Electrical Commercial and Industrial](#) > [Products](#) > [Electrical Commercial & Industrial Products Catalog](#) > [Electrical Tape, Mastics & Special Use](#) > [Vinyl Electrical Tapes](#) > [Scotch® Super 33+™ Vinyl Electrical Tape, 3/4 in x 66 ft](#)

[Find An Account Rep](#)[Where To Buy \(Find A Distributor\)](#)[Contact Us](#)

# Scotch® Super 33+™ Vinyl Electrical Tape, 3/4 in x 66 ft

3M ID 80610833834 UPC# 00054007061328 UPC# 00076308624125 Part Number 33+SUPER-3/4X66FT

[Print](#)

Scotch® Super 33+™ Vinyl Electrical Tape is a premium grade, 7 mil thick, all-weather vinyl-insulating tape. It is designed to perform continuously between a temperature range of 0–220°F (-18–105°C). It has an excellent resistance to abrasion, moisture, alkalies, acids, corrosion and varying weather conditions (including ultraviolet exposure).

- 3/4 in x 66 ft, Black
- Premium grade, 7 mil thick, all-weather vinyl-insulating tape
- Temperature range of 0–220°F (-18–105°C)
- Excellent resistance to abrasion, moisture, alkalies, acids, corrosion and varying weather conditions
- Provides moisture-tight electrical and mechanical protection with minimum bulk
- UL Listed and CSA Certified

[Need Help?](#)

**Questions?** We can help  
[Contact Us](#)



### Overview

### Documents

The combination of elastic backing and aggressive adhesive provides moisture-tight electrical and mechanical protection with minimum bulk. Scotch® Super 33+™ Vinyl Electrical Tape is an UL Listed and CSA Certified insulating tape.

### Specifications

<b>Adhesive Material</b>	Rubber Resin
<b>Agency Approvals</b>	CSA Certified, UL Listed
<b>Backing Material</b>	Polyvinyl Chloride
<b>Brand</b>	Super 33+™
<b>Breaking Strength</b>	15 lb/in
<b>Color</b>	Black
<b>Dielectric Strength</b>	1150 V/mil
<b>Family</b>	Scotch® Super 33+™ Vinyl Electrical Tape
<b>Length</b>	66 Linear Foot
<b>Length (Metric)</b>	20.1 m
<b>Material</b>	PVC
<b>Operating Temperature Range (Celsius)</b>	-18 to 105 Degree Celsius
<b>Operating Temperature Range (Fahrenheit)</b>	0 to 220 Degree Fahrenheit
<b>Product Family</b>	Scotch® Super 33+™ Vinyl Electrical Tape
<b>Product Type</b>	Vinyl Tape
<b>RoHS 2011/65/EU Compliant</b>	Yes
<b>RoHS EU Comments</b>	RoHS 2011/65/EU compliant without exemption *Important RoHS information
<b>Rolls per Carton</b>	10
<b>Rolls per Case</b>	100

<b>Self-Extinguishing</b>	Yes
<b>Self Sticking/Amalgamating</b>	No
<b>Solution for</b>	Wireless Network: Weatherproofing
<b>Specifications</b>	ASTM D-3005 Type 1
<b>Tape Grade</b>	Premium
<b>Tape Type</b>	Vinyl
<b>Thickness</b>	7 mil
<b>Thickness (Metric)</b>	0.177 mm
<b>Trademark</b>	Scotch
<b>UV Resistant</b>	Yes
<b>Voltage Application</b>	Low Voltage
<b>Vulcanizing</b>	No
<b>Width</b>	0.75 Inch
<b>Width (Metric)</b>	19

Manufacturing Origin: USA

The designation that a product is Manufactured in the USA means the product undergoes substantial transformation in one of our U.S. Manufacturing plants. Some products contain imported components.

Note: 3M products offered on a government contract that require country of origin representation must be certified by 3M Trade Compliance. Contact customer service at 800-245-3573 to request a certificate.

**3M:** [News](#) | [Careers](#) | [Partners & Suppliers](#) | [Investor Relations](#) | [SDS Search](#) | [Transport Information Search](#) | [Help Center](#)

[Legal Information](#) | [Privacy Policy](#)

© 3M 2017. All Rights Reserved.