


## Grounding - Zinc

### Images



[Download Photo Image](#)

[Download Dimensional Image](#)

Dimension A in Inches: 2.49  
Dimension B in Inches: 3.46  
Dimension C in Inches: 0.73  
Dimension D in Inches: 2.87  
Dimension E in Inches: 4.00

### Application

Used in situations where wires have already been pulled through conduit or EMT fittings, and an insulated Grounding bushing is required. Grounding lug; aluminum alloy 6061-T6. Rated 150 Degree C. cULus listed to UL514B and UL467 specifications. Patented

### Product Information

Material: Zinc Alloy  
Finish: Ball Burnished, Mirror Smooth,  
Grounding lug: Tin Electro-plate

### Certifications & Codes:

Federal Specification Number: A-A-50553  
NEMA Standard: FB-1  
UL File Number: E20412  
UL Standard: UL514B,UL467  
UNSPSC: 39121312  
Patent Number: 7,182,611; 6,840,782;  
8,419,449

**Catalog ID:** SGB-388CL

**UPC Number:** 78174790388

**Description:** Split Bushing, Insulated, Grounding, Zinc Die Cast, Size 3 Inch, 14-1/0 Lug

**Application:** Used in situations where wires have already been pulled through conduit or EMT fittings, and an insulated Grounding bushing is required. Grounding lug; aluminum alloy 6061-T6. Rated 150 Degree C. cULus listed to UL514B and UL467 specifications. Patented

**Trade Size:** 3"

**Std Pkg Qty:** 25