



Image File Name:
F594-PW--
1377184850.jpg

Item #: F594-PW	UPC Code: 706411039898
Product Family Name: Traditional Concept™	Finish: Pewter
Category: Exterior Fan	Category Type: Ceiling Fan
Certification E75795	
Patents	
Notes:	



MEASUREMENTS

Blade Finish:	Reversible Blades:	
	No	
Blade Material:	Slope:	
ABS Construction	No	
Blade Sweep:	No. of Blades:	Blade Pitch:
52	3	14 degrees
Downrod 1:	Downrod 2:	Hanging Weight:
Downrod 1 Outside Dia:	Downrod 2 Outside Dia:	22.53
Ceiling to Lowest Point: (Dim A)	Ceiling to Blade: (Dim B)	Lead Wire:
11.00	7.50	8
		Motor Size:
		172X20MM

	Low:	Low/Med:	Medium:	Med/High:	High:
RPM:	60		116		178
Amps:	0.28		0.46		0.50
Watts:	14.000		33.500		60.500
CFM:	2760.00		5074.13		6565.40
CFM/Watts	197.14		151.47		108.52



FAN CONTROLS

Pull Chain Control: No	Works with Remote Control: Yes	Works with Wall Control: Yes
	Included Remote Control:	Included Wall Control: WCS212
	Compatible Remote Control[s]: RCS212	Compatible Wall Control[s]:

LAMPING

No. of Bulbs: 1	Light Type: Mini-Can Halogen
Max Bulb Wattage: 100	Socket: E11
Light Kit: Yes	Dimmable: Yes
Lamp Included: Yes	Ballast:
	Rated Life Hours:
	Uplight
	Color Temp.:
	CRI:
	Initial Lumens:
	Delivered Lumens:

GLASS

Description:	Material: Glass
Part No.: RM191	Quantity: 1
Width:	Length:
Height:	



SHIPPING

Carton Width: 13.000	Carton Height: 12.880	Carton Length: 23.750
Carton Weight: 24.948	Carton Cubit Feet: 2.301	Small Package Shippable: Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
		Master Pack: 1



Wet Location

Yes



Title 17

Yes



UL Listed

Yes