



GE  
Lighting

14878 - GE Soft White R20

45R20MI/1-6PK

#### GENERAL CHARACTERISTICS

Base Description	Medium Screw
Base Type	Screw-In
Bulb Finishes and Colors	Soft white
Filament	CC-6
Life in Years	1.8 yr
Rated Life Hours-nominal	2000 h
Product Technology	Incandescent
Base	E26
Bulb Shape	R20

#### PHOTOMETRIC CHARACTERISTICS

Nominal Initial Lumen per Watt	9
Initial Lumens-nominal	310 lm
Color Temperature	2600 K

#### PRODUCT INFORMATION

Product Code	14878
Description	45R20MI/1-6PK
Alternative Unit Of Measure	EACH
Standard Package Quantity	30
Ean UPC	043168906821
Standard Package GTIN	00043168906821
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	30
Sales Unit	Each
UCC	043168148788
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168906821
Standard Package GTIN	00043168148788
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168148788

#### ELECTRICAL CHARACTERISTICS

Wattage	45 W
Estimated Energy Cost per Year	5.42 \$
Input Voltage [nom]	120 V