



GE
Lighting

14891 - GE soft white 30 watt R20 floodlight 1-pack

30R20/1-6PK

- ☞ Use original GE's Soft White when you need a light without glare and harsh shadows.
- ☞ Replace ordinary light bulbs with GE Flood and Spotlight in all your track and recessed lighting fixtures.
- ☞ 2500K soft white light appearance
- ☞ GE soft white indoor spotlights provide warm, pleasing everyday light without harsh glares and shadows. These bulbs' funnel shape and reflective coating help direct light where it is needed better than a standard incandescent bulb
- ☞ Lasts 1.8 years based on 3 hours per day usage
- ☞ R20 indoor floodlight with medium base for use in directional fixtures such as recessed can lighting
- ☞ 140 lumens providing subtle, reassuring™ light
- ☞ Estimated yearly energy costs \$3.61 based on 3 hours per day \$0.11 per kWh

GENERAL CHARACTERISTICS

Base Description	Medium Screw
Base Type	Screw-In
Filament	CC-6
Rated Life Hours-nominal	2000 h
Primary Application	Indoor Floodlight
Bulb Material	Soft glass
Product Technology	Incandescent
Base	E26
Bulb Shape	R20

PHOTOMETRIC CHARACTERISTICS

Nominal Initial Lumen per Watt	7
Initial Lumens-nominal	140 lm
Color Temperature	2500 K

PRODUCT INFORMATION

Product Code	14891
Description	30R20/1-6PK
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168906623
Standard Package GTIN	00043168148917
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168148917
Alternative Unit Of Measure	EACH
Standard Package Quantity	30
Ean UPC	043168906623
Standard Package GTIN	00043168906623
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	30
Sales Unit	Each
UCC	043168148917

DIMENSIONS

Diameter	2.5 in
----------	--------

ELECTRICAL CHARACTERISTICS

Wattage	30 W
Input Voltage [nom]	120 V