



GE
Lighting

15199 - GE A15

40A15

GENERAL CHARACTERISTICS

Base Description	Medium Screw
Base Type	Screw-In
Bulb Finishes and Colors	Clear
Filament	C-9
Life in Years	1.4 yr
Rated Life Hours-nominal	1500 h
Primary Application	Standard <General Purpose> Ceiling Fan
Bulb Material	Soft glass
Product Technology	Incandescent
Base	E26
Bulb Shape	A15

PHOTOMETRIC CHARACTERISTICS

Nominal Initial Lumen per Watt	10
Initial Lumens-nominal	415 lm
Color Temperature	2600 K

PRODUCT INFORMATION

Product Code	15199
Description	40A15
Alternative Unit Of Measure	EACH
Standard Package Quantity	120
Ean UPC	043168910088
Standard Package GTIN	00043168910088
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	120
Sales Unit	Each
UCC	043168151993
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168910088
Standard Package GTIN	00043168151993
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168151993

DIMENSIONS

Diameter	1.87 in
----------	---------

ELECTRICAL CHARACTERISTICS

Wattage	40 W
Estimated Energy Cost per Year	4.82 \$
Input Voltage [nom]	120 V