



PRODUCT DESCRIPTION

Maxim Lighting's slim 2.5" profile Energy Star Certified Low Profile EE Collection uses energy saving T9 Circline bulbs, mountable on the ceiling or wall, with features including electronic no flicker ballasts, 3100 K color temperature, rated life of 10,000 hours, and UV rated acrylic.

FINISHES OPTION



GLASS

White WT

MATERIAL

Acrylic, Steel


RATINGS

cULus
Damp Location
CA Title 24



ADDITIONAL

INCANDESCENT WATTS: 432
RATED LIFE 15000+18000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)




MEASUREMENTS

DIMENSION : 19.5" L x 19.5" W x 3.5" H
MAX OAH : 17" W x 17" H
HANGING WEIGHT : 5.8 lb

LAMPING

INPUT VOLTAGE : 120V
LUMENS : 4,750 Rated
BULB : 2 x 32+40W Fluorescent 4-Pin T9 Circline , 72W Total
BULB INCLUDED : (Included)
DIMMABLE : No
COLOR_TEMP : 3100K



Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746
EASTERN DISTRIBUTION CENTER
4200 SHIRLEY DR. | ATLANTA, GA 30336
P. 626.956.4200 | F. 626.956.4225 | maximlighting.com