



GE
Lighting

15777 - GE CA10

25CAC 25PK

Product Photo



GENERAL CHARACTERISTICS

| | |
|--------------------------|-------------------------------------|
| Base Description | Candelabra Screw |
| Base Type | Screw-In |
| Bulb Finishes and Colors | Clear |
| Filament | CC-2V |
| Life in Years | 1.4 yr |
| Rated Life Hours-nominal | 1500 h |
| Primary Application | Standard <Decorative> Chandelier |
| Bulb Material | Soft glass |
| Product Technology | Incandescent |
| Base | E12 |
| Bulb Shape | CA10 |

PHOTOMETRIC CHARACTERISTICS

| | |
|------------------------|--------|
| Initial Lumens-nominal | 220 lm |
| Color Temperature | 2500 K |

PRODUCT INFORMATION


| | |
|----------------------------------|----------------|
| Product Code | 15777 |
| Description | 25CAC 25PK |
| Alternative Unit Of Measure | CASE |
| Standard Package Quantity | |
| Ean UPC | 043168157773 |
| Standard Package GTIN | 10043168157770 |
| No Of Items Per Sales Unit | |
| No Of Items Per Standard Package | |
| Sales Unit | Case |
| UCC | 043168157773 |
| Alternative Unit Of Measure | EACH |
| Standard Package Quantity | 200 |
| Ean UPC | 043168157773 |
| Standard Package GTIN | 00043168157773 |
| No Of Items Per Sales Unit | 1 |
| No Of Items Per Standard Package | 200 |
| Sales Unit | Each |
| UCC | 043168157773 |
| Alternative Unit Of Measure | PACK |
| Standard Package Quantity | |
| Ean UPC | 043168157773 |
| Standard Package GTIN | 30043168157774 |
| No Of Items Per Sales Unit | |
| No Of Items Per Standard Package | |
| Sales Unit | Inner Pack |
| UCC | 043168157773 |

DIMENSIONS

| | |
|----------|---------|
| Diameter | 1.25 in |
|----------|---------|

ELECTRICAL CHARACTERISTICS

| | |
|--------------------------------|--|
| Burn Position | Horizontal $\pm 15^\circ$ or Base Down |
| Wattage | 25 W |
| Estimated Energy Cost per Year | 3.01 \$ |
| Input Voltage [nom] | 120 V |



Jan 6, 2017 11:19:53 AM For additional information, visit www.gelighting.com