



GE  
Lighting

15781 - GE CA10

60CAC 25PK

Product Photo



### GENERAL CHARACTERISTICS

Base Description	Candelabra Screw
Base Type	Screw-In
Bulb Finishes and Colors	Clear
Filament	CC-2V
Life in Years	1.4 yr
Rated Life Hours-nominal	1500 h
Primary Application	Standard <Decorative> Chandelier
Bulb Material	Soft glass
Product Technology	Incandescent
Base	E12
Bulb Shape	CA10

### PHOTOMETRIC CHARACTERISTICS

Initial Lumens-nominal	650 lm
Color Temperature	2500 K

### PRODUCT INFORMATION

Product Code	15781
Description	60CAC 25PK
Alternative Unit Of Measure	EACH
Standard Package Quantity	200
Ean UPC	043168157810
Standard Package GTIN	00043168157810
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	200
Sales Unit	Each
UCC	043168157810
Alternative Unit Of Measure	PACK
Standard Package Quantity	
Ean UPC	043168157810
Standard Package GTIN	30043168157811
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Inner Pack
UCC	043168157810
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168157810
Standard Package GTIN	10043168157817
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168157810

### DIMENSIONS

Diameter	1.25 in
----------	---------

### ELECTRICAL CHARACTERISTICS

Wattage	60 W
Estimated Energy Cost per Year	7.23 \$
Input Voltage [nom]	120 V



Jan 6, 2017 11:23:41 AM For additional information, visit [www.gelighting.com](http://www.gelighting.com)