



GE
Lighting

15790 - GE G16.5

25GC 25PK

Product Photo



GENERAL CHARACTERISTICS

Base Description	Candelabra Screw
Base Type	Screw-In
Bulb Finishes and Colors	Clear
Filament	CC-2V
Life in Years	1.4 yr
Rated Life Hours-nominal	1500 h
Primary Application	Globe
Bulb Material	Soft glass
Product Technology	Incandescent
Base	E12
Bulb Shape	G16.5

PHOTOMETRIC CHARACTERISTICS

Initial Lumens-nominal	195 lm
Color Temperature	2500 K

PRODUCT INFORMATION


Product Code	15790
Description	25GC 25PK
Alternative Unit Of Measure	PACK
Standard Package Quantity	
Ean UPC	043168157902
Standard Package GTIN	30043168157903
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Inner Pack
UCC	043168157902
Alternative Unit Of Measure	EACH
Standard Package Quantity	100
Ean UPC	043168157902
Standard Package GTIN	00043168157902
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	100
Sales Unit	Each
UCC	043168157902
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168157902
Standard Package GTIN	10043168157909
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168157902

DIMENSIONS

Diameter	2.06 in
----------	---------

ELECTRICAL CHARACTERISTICS

Wattage	25 W
Estimated Energy Cost per Year	3.01 \$
Input Voltage [nom]	120 V



Jan 6, 2017 11:20:11 AM For additional information, visit www.gelighting.com