



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Series G, JG-frame Molded Case Circuit Breaker

**JGE3150FAG**

**UPC:782113526713**

### Dimensions:

- **Height:** 7 IN
- **Length:** 3.57 IN
- **Width:** 4.13 IN

**Weight:**6 LB

### Warranties:

### Specifications:

- **Type:** Complete breaker
- **Amperage Rating:** 150A
- **Interrupt Rating:** 65 kAIC at 240V, 25 kAIC at 415V, 25 kAIC at 480V, 18 kAIC at 600V
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 600V
- **Frame Size:** JG-frame
- **Series:** Series G
- **Terminals:** Line and load
- **Trip Type:** Fixed thermal, adjustable magnetic
- **Mounting Hardware:** Metric

### Supporting documents:

- [Eatons Volume 4-Circuit Protection](#)
- [AB DE-ION CIRCUIT BREAKER TYPE JG BRKR JG CURR LIMITER 3 POLE OUTLINE](#)
- [JG-frame Molded Case Circuit Breaker Drawing](#)
- [Installation Instructions for Series G J-Frame Circuit Breakers](#)
- [J-Frame 310+ and L-Frame 310+ Molded-case circuit breakers](#)
- [Series G, J-frame Time Current Curve](#)

### Certifications:

- CSA Certified



- IEC Rated
- UL Listed

**Product compliance:**

- CE Marked

---

© 2016 Eaton. All rights reserved.