



GE
Lighting

15831 - GE Soft White Spiral® T3 - Facilities; Retail Display;

Hospitality; Office; Restaurant

FLE15HT3/2/827

- ☞ Up to 75% energy savings
- ☞ One piece unit screws directly into incandescent sockets
- ☞ T3 Spirals® lamps provide economical solution with small overall size

Product Photo



GENERAL CHARACTERISTICS

Base Type	Screw-In
Mercury Content	3.5 mg
Rated Life Hours-nominal	10000 h
Starting Temp (MIN) C-degrees	-15 °C
Base Description	Medium Screw
Mercury-Picogram per mean lm hr	571.9
Primary Application	Standard <General Purpose> Facilities Retail Display Hospitality Office Restaurant

Product Technology	Compact Fluorescent
Base	E26
Bulb Shape	T5

PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	765 lm
Nominal Initial Lumen per Watt	63
Initial Lumens-nominal	950 lm
Color Rendering Index-CRI	82
Color Temperature	2700 K

PRODUCT INFORMATION

Product Code	15831
Description	FLE15HT3/2/827
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168158312
Standard Package GTIN	10043168158319
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168158312
Alternative Unit Of Measure	EACH
Standard Package Quantity	10
Ean UPC	043168158312
Standard Package GTIN	00043168158312
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	10
Sales Unit	Each
UCC	043168158312

DIMENSIONS

Nominal Length	4.8 in
Bulb Max Overall Length-MOL	4.8 in

ELECTRICAL CHARACTERISTICS

Equivalent Incandescent Watts	60 W
Rated power (Watts)	15 W

CAUTIONS & WARNINGS

NOTES

Best performance if operated base up and at 77 degrees F (25C) ambient temperature.