

shat-r-shield[®] INC.

01697W

250R40/HT/CLEAR (PK X 12)



Application:	Offices, Schools, Restaurants, Medical, Retail, Hospitality, General Lighting	Average Life Hours:	5000
Base:	Medium (E26)	Bulb:	R40
Coating:	PFA	Kelvin:	2700
CRI:	100	Diameter:	5.00 IN
Finish:	Clear	Initial Lumens:	1200
Pack By:	12	Weight:	0.442
Length:	6.50 IN	Mean Lumens:	1200
SDS:	Download SDS	Package Dimensions:	7.40 x 14.50 x 19.00
Package Weight:	5.30 L	Shape:	R40
Special Features:	Shatter-Resistant	Type:	Incandescent
UNSPSC:	39101612	UPC:	726585016976
Volts:	120	Wattage:	250.0

UL Listed, NSF Approved