



Electrical Commercial and Industrial

[Products](#) | [Documentation & Literature](#) | [News & Tradeshows](#) | [Support](#)


[United States](#) > [Energy](#) > [Electrical Commercial and Industrial](#) > [Products](#) > [Electrical Commercial & Industrial Products Catalog](#) > [Electrical Tape, Mastics & Special Use](#) > [Vinyl Electrical Tapes](#) > 3M™ Temflex™ General Use Vinyl Electrical Tape 1700C, 3/4 in x 66 ft, Brown

[Find An Account Rep](#)[Where To Buy \(Find A Distributor\)](#)[Contact Us](#)

3M™ Temflex™ General Use Vinyl Electrical Tape 1700C, 3/4 in x 66 ft, Brown

3M ID 80610736896 UPC# 00054007506492 Part Number 1700C-BROWN

[Print](#)



3M™ Temflex™ Vinyl Electrical Tape 1700 is a good quality, economical, general purpose vinyl insulating tape. It has excellent resistance to abrasion, moisture, alkalies, acid, copper corrosion and varying weather conditions. It is a polyvinyl chloride (PVC) tape that is flame-retardant and conformable.

- 3/4 in x 66 ft, Brown
- General purpose vinyl insulating tape
- Excellent resistance to abrasion, moisture, alkalies, acid, copper corrosion and varying weather conditions
- Polyvinyl chloride (PVC) tape that is flame-retardant and conformable
- Used for protective jacketing and harnessing
- Mechanical protection with minimum bulk
- UL Listed and CSA Certified

Need Help?

Questions? We can help
[Contact Us](#)

Overview

Documents

Tape is used for protective jacketing and harnessing. Provides excellent mechanical protection with minimum bulk. UL Listed and CSA Certified for 176°F (80°C).

Specifications

Adhesive_Material	Rubber Resin
Agency_Approvals	CSA Certified, UL Listed
Backing_Material	Polyvinyl Chloride
Brand	Temflex™
Breaking_Strength	17 lb/in
Color	Brown
Dielectric_Strength	1000 V/mil
Length	66 Linear Foot
Length_metric	20.1 m
Operating_Temperature_Range_Celsius	0 to 80 Degree Celsius
Operating_Temperature_Range_Fahrenheit	32 to 176 Degree Fahrenheit
Product_Type	Vinyl Electrical Tapes
RoHS_2011_65_EU_Compliant	Yes
RoHS_EU_Comments	RoHS 2011/65/EU compliant without exemption *Important RoHS information
Specifications	ASTM D 2301 Type 1
Tape_Grade	General Use
Tape_Type	Vinyl
Thickness	7 mil
Thickness_metric	0.177 mm
Voltage_Application	Low Voltage
Width	0.75 Inch
Width_metric	19 mm

