

MINKA-LAVERY®

Item #: 1421-84	UPC Code: 747396044705
Product Family Name: Paradox™	Finish: BRUSHED NICKEL
Category: Mini-Pendants	Category Type: Mini Pendant
Certification E127416	
Patents	
Notes: *Also available 1421-281	



Image File Name:
1421-84--
1377121171.jpg



MEASUREMENTS

Width: 6.5	Length: 6.5	Height: 5.5	Extension: 6.5
Height Adjustable: Yes	Min Overall Height: 13.50	Max Overall Height: 49.50	Slope: Yes
Wire Length: 72	Chain Length: 1.00	Safety Cable Included: No	Net Weight: 3.37
Canopy Width: 5.00	Canopy Height: 1.00	Canopy Length: 6.38	
Backplate Width:	Backplate Height:	Center to Top:	Center to Bottom:

LAMPING

No. of Bulbs: 1	Light Type: A19 Med			
Max Bulb Wattage: 100	Socket: E26 Med			
Dimmable: Yes	Ballast:	Rated Life Hours:	Photocell Included:	Lamps Included: No
Lamp Included: No	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:

SHADE / GLASS

Description:	Material: Glass
Part No.: G5421	Quantity: 1
Width: 6.38	Height: 4.50
	Length: 6.38



SHIPPING

Carton Width: 9.000	Carton Height: 8.500	Carton Length: 13.000
Carton Weight: 4.990	Carton Cubic Feet: 0.576	Small Package Shippable: Yes
Master Pack Width: 13.750	Master Pack Height: 17.750	Master Pack Length: 19.000
Master Pack Weight: 20.878	Master Cubic Feet:	Multi-Pack: 1
		Master Pack: 4



Title 17

Yes



UL Listed

Yes