



Image File Name:
F522-WH_0.jpg

Item #: F522-WH	UPC Code: 706411044038
Product Family Name: Mojo	Finish: White
Category: Interior Fan	Category Type: Ceiling Fan
Certification 4000048	
Patents	
Notes:	



MEASUREMENTS

Blade Finish:	Reversible Blades:		
	No		
Blade Material:	Slope:		
Plywood Construction	No		
Blade Sweep:	No. of Blades:	Blade Pitch:	Hanging Weight:
52	5	12	17.48
Downrod 1:	Downrod 1 Outside Dia:	Downrod 2:	Downrod 2 Outside Dia:
3.5	.75	6	.75
Ceiling to Lowest Point: (Dim A)	Ceiling to Blade: (Dim B)	Lead Wire:	Motor Size:
11.75	9.00	80	153x15mm

	Low:	Low/Med:	Medium:	Med/High:	High:
RPM:	85		135		180
Amps:	0.27		0.42		0.55
Watts:	14.100		34.100		65.700
CFM:	2370.00		3750.00		5295.00
CFM/Watts:	168.09		109.97		80.59



FAN CONTROLS

Pull Chain Control:	Works with Remote Control:	Works with Wall Control:
Yes	Yes	Yes
	Included Remote Control:	Included Wall Control:
	Compatible Remote Control[s]:	Compatible Wall Control[s]:
	RCS213,RCS223	WC106,WCS213,WCS223

LAMPING

No. of Bulbs:	Light Type:			
3	B10.5, Cand			
Max Bulb Wattage:	Socket:			
60	E12			
Light Kit:	Dimmable:	Ballast:	Rated Life Hours:	Uplight
Yes	Yes			
Lamp Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
Yes				

GLASS

Description:	Material:
	Glass
Part No.:	Quantity:
GF522	1
Width:	Height:
	Length:



SHIPPING

Carton Width:	Carton Height:	Carton Length:	
13.380	11.000	23.000	
Carton Weight:	Carton Cubit Feet:	Small Package Shippable:	
20.570	1.959	Yes	
Master Pack Width:	Master Pack Height:	Master Pack Length:	
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:	Master Pack:
			1



Title 17

Yes



ETL Intertek

Yes

For additional information, please contact Customer Care: 1-800-221-7977

Product depicted on this spec sheet is protected by United States Federal and/or State laws including US Patent, Trademark and/or Copyright and unfair competition laws. Unauthorized reproduction or use carries severe legal penalties