



Electrical Commercial and Industrial

[Products](#) | [Documentation & Literature](#) | [News & Tradeshows](#) | [Support](#)

[United States](#) > [Energy](#) > [Electrical Commercial and Industrial](#) > [Products](#) > [Electrical Commercial & Industrial Products Catalog](#) > [Electrical Tape, Mastics & Special Use](#) > [Mastic Tapes - Sealing and Insulating](#) > [Scotch® Rubber Mastic Tape 2228, 1 in x 10 ft](#)

[Find An Account Rep](#) [Where To Buy \(Find A Distributor\)](#) [Contact Us](#)

Scotch® Rubber Mastic Tape 2228, 1 in x 10 ft

3M ID 80610737662 UPC# 00054007507277 Part Number 2228-1X10FT

[Print](#)



Scotch® Rubber Mastic Tape 2228 is a conformable self-fusing rubber electrical insulating and sealing tape. Tape consists of Ethylene Propylene Rubber (EPR) backing coated with a strong, temperature-stable mastic adhesive.

- 1 in x 10 ft
- Conformable self-fusing rubber electrical insulating and sealing tape
- Ethylene Propylene Rubber (EPR) backing coated with a strong, temperature-stable mastic adhesive
- Use to insulate, pad, and seal bus bar and splice connections
- Temperature rated at 194°F (90°C)

Need Help? [ire](#)

Questions? We can help
[Contact Us](#)



Overview | **Documents**

Use Scotch® Rubber Mastic Tape 2228 to insulate, pad, and seal bus bar and splice connections. It's temperature rated at 194°F (90°C).

Specifications

Adhesion to Steel	26 N/cm
Adhesive Material	Mastic
Backing Material	Ethylene Propylene Rubber
Backing Thickness (metric)	165 mm
Brand	Scotch
Breaking Strength	17 N/cm
Color	Black
Dielectric Strength	500 V/mil
Dielectric Strength (V/mil)	500
Elongation	1000 %
Elongation at Break	100%
Family	Scotch® Rubber Mastic Tape 2228
Length	10 Linear Foot
Length (Metric)	3 m
Liner/Linerless	Liner
Material	Ethylene Propylene Rubber and Mastic
Operating Temperature (Celsius)	Up to 90 Degree Celsius
Operating Temperature (Fahrenheit)	Up to 194 Degree Fahrenheit
Operating Temperature Range (Celsius)	Up to 90 Degree Celsius

Operating Temperature Range (Fahrenheit)	Up to 194 Degree Fahrenheit
Product Family	Scotch® Rubber Mastic Tape 2228
RoHS 2011/65/EU Compliant	Yes
RoHS EU Comments	RoHS 2011/65/EU compliant without exemption *Important RoHS information
Rolls per Case	12
Self-Extinguishing	No
Self Sticking/Amalgamating	Yes
Shelf Life	5 Year
Solution for	Access Network: FTTH/FTTB/CATV, Wireless Network: Weatherproofing, Access Network: xDSL, Long-haul/Metro Loop Network: Outdoor
Suitable for High Voltage	Yes
Tape Color	Black
Tape Grade	Premium
Tape Type	Sealing and Mastic
Thickness	65 mil
Thickness (Metric)	1.65 mm
Trademark	Scotch
UV Resistant	Yes
Voltage Application	High Voltage
Vulcanizing	No
Width	1 Inch
Width (Metric)	25 mm

Manufacturing Origin: USA

The designation that a product is Manufactured in the USA means the product undergoes substantial transformation in one of our U.S. Manufacturing plants. Some products contain imported components.

Note: 3M products offered on a government contract that require country of origin representation must be certified by 3M Trade Compliance. Contact customer service at 800-245-3573 to request a certificate.

3M: [News](#) | [Careers](#) | [Partners & Suppliers](#) | [Investor Relations](#) | [SDS Search](#) | [Transport Information Search](#) | [Help Center](#)

[Legal Information](#) | [Privacy Policy](#)

© 3M 2017. All Rights Reserved.