

## VS10604-GBZ: 4 - Light Vanity Fixture

### Dimensions:

**Length:** 31"                      **Extends:** 6 1/2"  
**Height:** 7 3/4"                      **Wire:** 8"  
**Weight:** 5.76 lbs.                      **Connection:** Mounted To Box

### Bulbs:

4 - Medium A19 100w Max. 120v - Not included

### Features:

•

### Material List:

### Safety Listing:

Safety Listed for Damp Locations / IC  
 Safety Listed for Damp Locations / IC

### Instruction Sheets:

English (2003\_2031)



**Collection:** Morningside

**UPC #:** 014817289312

**Finish:** Grecian Bronze (GBZ)

### Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate				5 1/2		

### Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Frt. Class	UPS Ship
Individual	VS10604-GBZ	1	014817289312	30	9	9	1.406	10.1	125	Yes
NJ Pallet		48		48	40	76	84.444	484.8		No
NV Pallet		48		48	40	76	84.444	484.8		No