



Item #: F843-SL	UPC Code: 706411044274
Product Family Name: Wave	Finish: Silver
Category: Interior Fan	Category Type: Ceiling Fan
Certification 4000048	
Patents D715,419; D715,421	
Notes:	

Image File Name:
F843-SL_0.jpg



MEASUREMENTS

Blade Finish:	Reversible Blades:				
	No				
Blade Material:	Slope:				
ABS Construction	No				
Blade Sweep:	No. of Blades:	Blade Pitch:	Hanging Weight:		
52	3	VARIABLE	12.37		
Downrod 1:	Downrod 1 Outside Dia:	Downrod 2:	Downrod 2 Outside Dia:		
4.5	.75	6	.75		
Ceiling to Lowest Point: (Dim A)	Ceiling to Blade: (Dim B)	Lead Wire:	Motor Size:		
13.00	9.50	80	172x14mm		
RPM:	Low:	Low/Med:	Medium:	Med/High:	High:
61			107		153
Amps:	0.23		0.39		0.55
Watts:	11.400		31.400		66.400
CFM:	2699.00		4537.00		6580.00
CFM/Watts	236.75		144.49		99.10



FAN CONTROLS

Pull Chain Control:	Works with Remote Control:	Works with Wall Control:
No	Yes	Yes
	Included Remote Control:	Included Wall Control:
	RCS213	
	Compatible Remote Control[s]:	Compatible Wall Control[s]:
		WCS213

LAMPING

No. of Bulbs:	Light Type:			
	N/A			
Max Bulb Wattage:	Socket:			
Light Kit:	Dimmable:	Ballast:	Rated Life Hours:	Uplight
No	No			
Lamp Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
No				

GLASS

Description:	Material:	
Part No.:	Quantity:	
Width:	Height:	Length:



SHIPPING

Carton Width:	Carton Height:	Carton Length:	
14.000	9.630	31.380	
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:	
16.810	2.448	Yes	
Master Pack Width:	Master Pack Height:	Master Pack Length:	
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:	Master Pack:
			1



ENERGY
STAR
Yes



Title 17
Yes



ETL Intertek
Yes