



GE
Lighting

16451 - GE Quartzline® T4

Q100DC

Product Photo



GENERAL CHARACTERISTICS

Base Description	Double Contact Bayonet
Base Type	Pin/Plug-In
Bulb Finishes and Colors	Frost
Filament	CC-8
Rated Life Hours-nominal	2000 h
Product Technology	Halogen
Base	BA15d
Bulb Shape	T4

PHOTOMETRIC CHARACTERISTICS

Nominal Initial Lumen per Watt	16
Initial Lumens-nominal	1550 lm
Color Temperature	2950 K

PRODUCT INFORMATION

Product Code	16451
Description	Q100DC
Alternative Unit Of Measure	CASE

DIMENSIONS

Diameter	0.5 in
Light Center Length	1.37 in

ELECTRICAL CHARACTERISTICS

Input Voltage [nom]	120 V
Rated power (Watts)	100 W

CAUTIONS & WARNINGS

Caution

- Lamp may shatter and cause injury if broken
- Dispose of lamp in a closed container.
- Do not use lamp if outer glass is scratched or broken.

Risk of Burn

- Allow lamp to cool before handling.
- Turn power off before installing lamp.

Warning

- Lamp emits UV radiation which may cause eye/skin irritation.
- Avoid exposure of eyes and skin to unshielded lamp.

Risk of Electric Shock

- Turn power off before inspection
- installation or removal.

Risk of Fire

- Keep combustible materials away from lamp.
- Use in enclosed fixture rated for this product.

Unexpected lamp rupture may cause injury, fire, or property damage

- Use eye protection when handling lamp.
- Use in enclosed fixture rated for this product.
- Do not touch glass with bare hands.
- Do not use lamp if outer glass is scratched or broken.
- Do not exceed 110% of rated voltage.