

FEISS

EST. 1955

OL1900GBZ: 1 - Light Wall Lantern



Dimensions:

Width: 7" **Extends:** 8 1/4"
Height: 11 3/4" **Wire:** 8"
Weight: 4.75 lbs. **Connection:** Mounted To Box

Bulbs:

1 - Medium A19 100w Max. 120v - Not included

Features:

- CFL Convertible. For commercial quotes, call 847.410.4602
-

Material List:

1 Body - Aluminum - Bronze

Safety Listing:

Safety Listed for Wet Locations

Instruction Sheets:

English (2019)

Collection: Castle

UPC #: 014817218763

Finish: Grecian Bronze (GBZ)

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate	7 1/2	4 1/2			4	7 3/4

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	OL1900GBZ	1	014817218763	13.5	8.5	9	0.598	4.7	125	Yes
NJ Pallet		84		48	40	73	81.111	394.8		No
NV Pallet		96		48	40	76	84.444	451.2		No