

HID

HIGH INTENSITY DISCHARGE BALLASTS



Ignitor Specifications (Case Temperature Rating 105° C)

High Pressure Sodium




High Pressure Sodium									
Ballast Data				Standard Ignitor			Long Range Ignitor		
Advance Ballast Family	Lamp Watts	ANSI Code	Ballast Circuit Type	Catalog Number	Max. Dist. (ft.) To Lamp	Case Type	Catalog Number	Max. Dist. (ft.) To Lamp	Case Type
71A7707	35	S76	R	LI551-H4-IC	2	Round	LI551-J4-IC	15	Round
71A77_5	35	S99	Hybrid	6C035-IC*	2	Rect	Not Available		
71A7801	50	S68	HX	LI551-H4-IC	2	Round	LI551-J4-IC	35	Round
71A7807	50	S68	R	LI551-H4-IC	2	Round	LI551-J4-IC	15	Round
71A78_5	50	S104	Hybrid	6C050-IC*	2	Rect.	Not Available		
71A79_0	70	S62	Reg Lag	LI551-H4-IC	2	Round	LI551-J4-IC	20	Round
71A79_1	70	S62	HX	LI551-H4-IC	2	Round	LI551-J4-IC	35	Round
71A79_6	70	S62	CWI	LI551-J4-IC	2	Round	Not Available		
71A79_8	70	S62	CWA	LI551-J4-IC	5	Round	Not Available		
71A7907	70	S62	R	LI551-H4-IC	2	Round	LI551-J4-IC	15	Round
71A80_0	100	S54	Reg Lag	LI551-H4-IC	2	Round	LI551-J4-IC	35	Round
71A80_1	100	S54	HX	LI551-H4-IC	2	Round	LI551-J4-IC	35	Round
71A80_8	100	S54	CWA	LI551-J4-IC	5	Round	Not Available		
71A8007	100	S54	R	LI551-H4-IC	2	Round	LI551-J4-IC	15	Round
71A80_6	100	S54	CWI	LI551-J4-IC	2	Round	Not Available		
71A80_5	100	S105	Hybrid	6C100-IC*	2	Rect.	Not Available		
71A81_0	150	S55	Reg Lag	LI551-H4-IC	2	Round	LI551-J4-IC	40	Round
71A81_2	150	S55	HX	LI551-H4-IC	2	Round	LI551-J4-IC	35	Round
71A81_8	150	S55	CWA	LI551-J4-IC	10	Round	Not Available		
71A8107	150	S55	R	LI551-H4-IC	2	Round	LI551-J4-IC	15	Round
71A8156	150	S55	CWI	LI551-J4-IC	2	Round	Not Available		
71A85_5	150	S55	CWI	LI551-J4-IC	2	Round	Not Available		
71A81_6	150	S56	CWA	LI501-H4-IC	2	Round	LI501-J4-IC	50	Round
71A86_7	150	S56	R	LI501-H4-IC	2	Round	LI501-J4-IC	50	Round

* - Case temperature rating is 80°C only.



CC-125
MOUNTING CLIP for Round Case
(Furnished as standard with -001
suffix ballasts and all -IC suffix
replacement ignitors.)



HID • IGNITORS
HPS

HIGH INTENSITY DISCHARGE BALLASTS

HID

Ignitor Specifications



(Case Temperature Rating 105° C)





High Pressure Sodium

High Pressure Sodium									
Ballast Data				Standard Ignitor			Long Range Ignitor		
Advance Ballast Family	Lamp Watts	ANSI Code	Ballast Circuit Type	Catalog Number	Max. Dist. (ft.) To Lamp	Case Type	Catalog Number	Max. Dist. (ft.) To Lamp	Case Type
71A89_0	200	S66	CWA	LI501-H4-IC	2	Round	LI501-J4-IC	50	Round
71A89_1	200	S66	CWA	LI501-H4-IC	2	Round	LI501-J4-IC	50	Round
71A89_4	200	S66	Reg Lag	LI501-H4-IC	2	Round	LI501-J4-IC	40	Round
71A89_7	200	S66	R	LI501-H4-IC	2	Round	LI501-J4-IC	50	Round
71A82_0	250	S50	Reg Lag	LI501-H4-IC	2	Round	LI501-J4-IC	50	Round
71A82_1	250	S50	CWA	LI501-H4-IC	2	Round	LI501-J4-IC	50	Round
71A82_6	250	S50	CWI	LI501-J4-IC	2	Round	Not Available		
71A82_7	250	S50	R	LI501-H4-IC	2	Round	LI501-J4-IC	50	Round
71A8392	250	S50	CWA	LI501-H4-IC	2	Round	LI501-J4-IC	50	Round
71A83_0	310	S67	Reg Lag	LI501-H4-IC	2	Round	LI501-J4-IC	50	Round
71A83_1	310	S67	CWA	LI501-H4-IC	2	Round	LI501-J4-IC	50	Round
71A83_7	310	S67	R	LI501-H4-IC	2	Round	LI501-J4-IC	50	Round
71A84_0	400	S51	Reg Lag	LI501-H4-IC	2	Round	LI501-J4-IC	50	Round
71A84_3	400	S51	CWA	LI501-H4-IC	2	Round	LI501-J4-IC	50	Round
71A84_6	400	S51	CWI	LI501-J4-IC	2	Round	Not Available		
71A84_7	400	S51	R	LI501-H4-IC	2	Round	LI501-J4-IC	50	Round
71A85_6	430	n/a	CWI	LI501-H4-IC	15	Round	LI501-J4-IC	35	Round
71A85_5	600	S106	CWA	LI561-H5-IC	5	Oval	Not Available		
71A85_8	600	S106	CWI	LI561-H5-IC	2	Oval	Not Available		
71A86_5	750	S111	CWA	LI561-H5-IC	5	Oval	Not Available		
71A87_3	1000	S52	CWA	LI571-H5-IC★	15	Oval	LI571-J5-IC★	75	Oval

★ Equipped with an auto-rest thermal protector to prevent ignitor from overheating in the event of lamp failure.



CC-125
MOUNTING CLIP for Round Case
(Furnished as standard with -001
suffix ballasts and all -IC suffix
replacement ignitors.)



HID • IGNITORS
HPS

