



Weatherproof Outlet Covers : Plastic & Extra-Duty Plastic

WP1030C | Plastic In-Use Weatherproof Cover - Double-Gang



WP1030C

PLASTIC IN-USE WEATHERPROOF COVER - DOUBLE-GANG

Plastic In-Use Weatherproof Covers are easy to install and include a gasket, mounting screws, base, cover assembly, and inserts to meet the needs of a variety of applications.



Features & Applications

Features

- Complies with 2014 NEC Article 314.15 for damp and wet locations
- Exceeds CEC Article 26-702
- UL Certified for Type 3R outdoor enclosures
- Meets requirements for cold impact testing: -60° F (-51° C)
- Heavy-duty UV stabilized polycarbonate cover, mounting base and inserts
- 1/8" (3 mm) thick neoprene gasket with slits for mounting screws
- Two inserts provided with all models for multiple installations
- Max cord size: (2) #14 AWG or (1) #12 AWG, WP1050 (2) #14 AWG or (1) #10 AWG
- Warranty: 1-year limited

Applications

- Industrial
- Commercial
- Manufacturing

- Residential
- Agricultural
- Signage
- Athletic Fields

Specifications

Gang Type

Double

Color

Clear

Is Extra Duty Rated

No

Hinge Direction

Vertical

Insert Types Included

WP101, WP102

Number of Included Inserts

2

Weatherproof Cover Material

UV Stabilized Plastic

Product Height (mm)

139.7

Product Width (mm)

127

Product Depth (mm)

79

Warranty

1-year limited

Resources & Support



NewsRoom

Get News, Product Info, Applications, Energy Savings and More...



Catalogs

Flip Through Our Products



Support

Easily Find Contact Information



Documents & Downloads

Find Wiring Diagrams, Instructions, Brochures, Video & More